



## How to Order

B



Model Shown: 6A-B6LJ2-SSP



Model Shown:  
6A-B6XJ2-SSP

Ports 1, 2, and 3			Valve Series	Seat Material	Seal Material	Body Material				
<b>1A</b>	1/16" A-LOK®	<b>SSP</b> 316 Stainless Steel <b>BP</b> Brass <b>MP</b> Monel® Alloy 400 <b>HCP</b> Hastelloy® C-276	<b>B2L</b> <b>B2X</b>	<b>J</b> PTFE <b>J2</b> PCTFE	<b>(Blank)</b> PTFE <b>V</b> Fluorocarbon Rubber <b>EPR</b> Ethylene Propylene Rubber <b>BN</b> Nitrile Rubber <b>KZ</b> Highly Fluorinated Fluorocarbon Rubber <b>LT</b> Live-Loaded PTFE Packing with PTFE Seals <b>VLT</b> Live-Loaded PTFE Packing with Fluorocarbon Rubber Seals <b>EPRLT</b> Live-Loaded PTFE Packing with Ethylene Propylene Rubber Seals <b>BNLT</b> Live-Loaded PTFE Packing with Nitrile Rubber Seals <b>KZLT</b> Live-Loaded PTFE Packing with Highly Fluorinated Fluorocarbon Rubber Seals					
<b>1Z</b>	1/16" CPI™									
<b>2A</b>	1/8" A-LOK®									
<b>2Z</b>	1/8" CPI™									
<b>2F</b>	1/8" Female NPT									
<b>2M</b>	1/8" Male NPT									
<b>4A</b>	1/4" A-LOK®									
<b>4Z</b>	1/4" CPI™									
<b>4M</b>	1/4" Male NPT									
<b>M3A</b>	3mm A-LOK									
<b>M3Z</b>	3mm CPI™									
<b>4A</b>	1/4" A-LOK®						<b>B6L</b> <b>B6X</b>	<b>J</b> PTFE <b>J2</b> PCTFE <b>S2</b> Spring-Loaded PCTFE <b>PKR</b> PTFE Lubricated PEEK <b>SPKR</b> Spring-Loaded PTFE Lubricated PEEK		
<b>4Z</b>	1/4" CPI™									
<b>4F</b>	1/4" Female NPT									
<b>4M</b>	1/4" Male NPT									
<b>4V</b>	1/4" VacuSeal									
<b>6A</b>	3/8" A-LOK®									
<b>6Z</b>	3/8" CPI™									
<b>6M</b>	3/8" Male NPT									
<b>M6A</b>	6mm A-LOK®									
<b>M6Z</b>	6mm CPI™									
<b>8A</b>	8mm A-LOK®	<b>B8L</b> <b>B8X</b>	<b>J</b> PTFE <b>J2</b> PCTFE <b>S2</b> Spring-Loaded PCTFE <b>PKR</b> PTFE Lubricated PEEK <b>SPKR</b> Spring-Loaded PTFE Lubricated PEEK							
<b>8Z</b>	1/2" CPI™									
<b>8F</b>	1/2" Female NPT									
<b>8M</b>	1/2" Male NPT									
<b>8V</b>	1/2" VacuSeal									
<b>12Z</b>	3/4" CPI™									
<b>12F</b>	3/4" Female NPT									
<b>M12A</b>	12mm A-LOK®									
<b>M12Z</b>	12mm CPI™									
<b>M16A</b>	16mm A-LOK®	<b>B8L</b> <b>B8X</b>	<b>J</b> PTFE <b>J2</b> PCTFE <b>S2</b> Spring-Loaded PCTFE <b>PKR</b> PTFE Lubricated PEEK <b>SPKR</b> Spring-Loaded PTFE Lubricated PEEK							
<b>M16Z</b>	16mm CPI™									

**Notes:**  
 1. Panel Mounting Nut supplied with each valve. Various port combinations are available.  
 2. See How to order.  
 3. VacuSeal is not available in Brass.  
 4. 12F (3/4" Female NPT) not panel mountable.

See examples on page 9. See pages 10 and 11 for information about How to Order Options and Maintenance Kits.